AC Filter Cost Optimized



Approvals and Compliances

Description

- Line filter in standard and medical version
- 1-stage
- standard attenuation

Characteristics

- Designed for standard applications
- Protection against interference voltage from the mains Possible interferences generated in the equipment are strongly attenu-
- Suitable for use in equipment according to IEC/UL 60950 Suitable for use in medical equipment according to IEC/UL 60601-1

Other versions on request

- Version with ZNR-varistor for overvoltage protection

References

Alternative: Standard version

Weblinks

pdf datasheet, html-datasheet, General Product Information, Distributor-Stock-Check, Detailed request for product, Microsite

Technical Data	
Ratings IEC	1 - 10 A @ Ta 40 °C / 250 VAC; 50 Hz
Ratings UL/CSA	1 - 10 A @ Ta 40 °C / 125 VAC; 60 Hz
Leakage Current	standard < 0.25 mA (250 V / 60 Hz)
Dielectric Strength	1.7 kVDC between L-N 2.7 kVDC between L/N-PE Test voltage (2 sec)
Allowable Operation Temperature	-25°C to 100°C
Climatic Category	25/100/21 acc. to IEC 60068-1
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140
Terminal	Quick connect terminals 6.3 x 0.8 mm
Material: Housing	Aluminum

Line Filter	Standard and Medical Version, IEC 60939, UL 1283, CSA C22.2 no. 8 Technical Details
MTBF	> 200'000h acc. to MIL-HB-217 F

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: FMLB

Approval Logo	Certificates	Certification Body	Description
10	VDE Approvals	VDE	Certificate Number: 40004673
	UL Approvals	UL	UL File Number: E72928

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
<u>IEC</u>	Designed according to	IEC 60320-1	Appliance couplers for household and similar general purposes
<u>IEC</u>	Designed according to	IEC 60939	Passive filters for suppressing electromagnetic interference
(I)	Designed according to	UL 498	Standard for Attachment Plugs and Receptacles
(I)	Designed according to	UL 1283	Electromagnetic interference filters
GF Group	Designed according to	CSA C22.2 no. 42	General Use Receptacles, Attachment Plugs, and Similar Wiring Devices
GF Group	Designed according to	CSA C22.2 no. 8	Electromagnetic interference (EMI) filters

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technologyequipment.
<u>IEC</u>	Designed for applications acc.	IEC 60601-1	Medical electrical equipment - Part 1: General requirements for basic safety and essential performance


Compliances


The product complies with following Guide Lines

Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
RoHS	RoHS	SCHURTER AG	EU Directive RoHS 2011/65/EU
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
	Medical Equipment	SCHURTER AG	Suitable for use in medical equipment according to IEC/UL 60601-1

Dimension [mm]

Case 41







1) Line 2) Load

Diagrams

Standard version

Medical version (M5)






1) Line

1) Line

2) Load

2) Load

Medical version (M80)




- 1) Line 2) Load

Attenuation Loss


- - - - 50Ω differential mode $\underline{\ }$ 50Ω common mode

Standard version


1 A




2 A




4 A



6 A




10 A




Medical version (M5)


1 A




2 A




4 A



6 A




10 A




Medical version (M80)


1 A




2 A




4 A



6 A



10 A



All Variants

Date of Comment	Filter Time	Laskana Cuu	I facilit	C+ (V0) [+F]	C+ (V0) [=F]	Majadak	Ususians	Ouder Number
Rated Current [A]	Filter-Type	Leakage Cur- rent [mA]	L [mH]	Cx (X2) [nF]	Cy (Y2) [nF]	Weight [g]	Housings	Order Number
1	Standard Version	0.25	2 x 10	68	2.2	50 g	41	5500.2026
2	Standard Version	0.25	2 x 4	68	2.2	50 g	41	5500.2027
4	Standard Version	0.25	2 x 1.5	68	2.2	50 g	41	5500.2028
6	Standard Version	0.25	2 x 0.8	68	2.2	65 g	41	5500.2029
10	Standard Version	0.25	2 x 0.3	68	2.2	65 g	41	5500.2030
1	Medical Version (M5)	0.005	2 x 10	68	-	50 g	41	5500.2077
2	Medical Version (M5)	0.005	2 x 4	68	-	50 g	41	5500.2078
4	Medical Version (M5)	0.005	2 x 1.5	68	-	50 g	41	5500.2079
6	Medical Version (M5)	0.005	2 x 0.8	68	-	65 g	41	5500.2080
10	Medical Version (M5)	0.005	2 x 0.3	68	-	65 g	41	5500.2081
1	Medical Version (M80)	0.08	2 x 10	68	0.47	50 g	41	5500.2089
2	Medical Version (M80)	0.08	2 x 4	68	0.47	50 g	41	5500.2090
4	Medical Version (M80)	0.08	2 x 1.5	68	0.47	50 g	41	5500.2091
6	Medical Version (M80)	0.08	2 x 0.8	68	0.47	65 g	41	5500.2092
10	Medical Version (M80)	0.08	2 x 0.3	68	0.47	65 g	41	5500.2093

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

25 Pcs Packaging unit