



Model H20® Incremental Encoder


BEISENSORS

Dimensions

Housing Type



Optional Face Mounts



Hollow Shaft





Figure 1

Output Waveform




Table A

H20 Disc Resolutions

| | | | | | | |
|------|------|-----|-----|-----|--------|----|
| 1* | 2 | 3 | 5 | 6 | 8 | 10 |
| 11 | 12 | 24 | 25 | 30 | | |
| 32 | 40 | 50 | 60 | 64 | | |
| 75 | 80 | 95 | 100 | 105 | 115 | |
| 120 | 125 | 150 | 192 | 200 | | |
| 240 | 250 | 256 | 300 | 336 | | |
| 360 | 400 | 500 | 510 | 512 | | |
| 600 | 625 | 635 | 720 | 785 | | |
| 1000 | 1024 | | | | 1200** | |

Resolutions Shown in **RED** are not available as Express Encoders

*No index. For interpolation please specify the multiplied output (up to 4,096 for H20) in the model number, i.e. 4,096-T4.

**Consult factory for this resolution

Notes

1. Mounting is usually done either using the D-style square flange mount, E- or G-style servo mounts, or one of the standard face mounts, F1 for example. Consult factory for additional face mount options.

2. The shaft seal is recommended in virtually all installations. The most common exceptions are applications requiring a very low starting torque or those requiring operation at both high temperature and high speed.

3. Non-standard index widths and multiple indices are available by special order. Consult factory.

4. Complementary outputs are recommended for use with line driver type (source/sink) outputs. When used with differential receivers, this combination provides a high degree of noise immunity.

5. **Output IC's:** Output IC's are available as either Line Driver (LD) or NPN Open Collector (OC) types. Open Collectors require pull-up resistors, resulting in higher output source impedance (sink impedance is similar to that of line drivers). In general, use of a Line Driver style output is recommended. Line Drivers source or sink current and their lower impedance mean better noise immunity and faster switching times. **Warning:** Do not connect any line driver outputs directly to circuit common/0V, which may damage the driver. Unused outputs should be isolated and left floating. Our applications specialists would be pleased to discuss your system requirements and the compatibility of your receiving electronics with Line Driver type outputs. **28V4:** Multi-voltage Line Driver (7272): 100 mA source/sink. Input voltage 5 to 28 VDC +/- 5% standard (Note: $V_{out} = V_{in}$). This driver is TTL compatible when used with 5 volt supply. Supply lines are protected against overvoltage to 60 volts and reverse voltage. Outputs are short circuit protected for one minute. Supply current is 120 mA typical (plus load current). This is the recommended replacement for 3904R and 7406R open collector outputs with internal pullup resistors. It is also a direct replacement for any 4469, 88C30, 8830 or 26LS31 line driver. **28V5:** Multi-voltage Line Driver (7272): 100 mA source/sink. Input voltage 5 to 28 VDC +/- 5% standard, internally regulated with 5V (TTL compatible) logic output. Supply lines are protected against overvoltage to 60 volts and reverse voltage. Outputs are short circuit protected for one minute. Supply current is 90 mA typical (plus load current). **15V4:** Multi-voltage Line Driver (4469): 100 mA source/sink. Input voltage 5 to 15 VDC +/- 5% standard (Note: $V_{out} = V_{in}$). TTL compatible when used with 5 volt supply. Supply lines are protected against overvoltage to 60 volts and reverse voltage. Outputs are short circuit protected for one minute. Supply current is 90 mA typical (plus load current). **15V5:** Multi-voltage Line Driver (4469): 100 mA source/sink. Input voltage 5 to 15 VDC +/- 5% standard (Note: $V_{out} = V_{in}$). TTL compatible when used with 5 volt supply. Supply lines are protected against overvoltage to 60 volts and reverse voltage. Outputs are short circuit protected for one minute. Supply current is 90 mA typical (plus load current). This is a direct replacement for the 4469 Line Driver. **28V/OC:** NPN Open Collector (3904*, 7273*). Current sink of 80 mA max. Current source by external pull-up resistor. Output can be pulled up to voltage other than supply voltage (30 V max). Input voltage 5 to 28 VDC +/- 5% standard. Supply current is 120 mA typical. This replaces prior IC's with designations of 3904, 7406, 3302, 681 and 689. **5V/OCR, 15V/OCR, 24V/OCR:** Open Collector (3904R*, 7406R*, 7273R*): Current sink of 70 mA max. Includes internal pull-ups sized at approximately 100 ohms/volt. Max current source is 10 mA. Supply current is 100 mA typical, 120 mA with internal pull-ups. 5V/5V/OC, 5V/OCR and 9V/OC can be intrinsically safe line driver and open collector outputs available on certain model variations. They are intrinsically safe only when installed per the control drawing noted on the certification label affixed to the encoder body.

6. Special -S at the end of the model number is used to define a variety of non-standard features such as special shaft lengths, voltage options, or special testing. Please consult the factory to discuss your special requirements.

7. Higher frequency response may be available. Please consult with the factory.

8. Extended temperature ratings are available in the following ranges: -40 to 70°C, -40 to 85°C, -20 to 105°C and -40 to 105°C depending on the particular model. Some models can operate down to -55°C. Extended temperature ranges can affect other performance factors. Consult with factory for more specific information.

9. Mating straight plug receptacles may be ordered from the factory:

For M12 use MS3116F12-10S, For M14 use MS3106F14S-6S

For M14/19 use MS3116J14-19S, For M16 use MS3106F16S-1S

For M18 use MS3106F18-1S, For M20 use MS3106F20-29S

* Products manufactured prior to April 2007 used the line driver IC number instead of voltage output in model number.

Table 1

Incremental Output Terminations

The connector style will determine pinouts. For example, an encoder with ABC channels and an M18 connector uses the table to the right.

| CHANNELS DESIGNATED IN MODEL NO. | | | |
|----------------------------------|-----|-------------------------------|-----|
| PIN | PIN | ABZ | ABC |
| E | A | A | A |
| D | B | B | B |
| C | C | Z | A |
| B | D | +V (SUPPLY VOLTAGE) | |
| F | E | — | B |
| A | F | 0 V (CIRCUIT COMMON) | |
| | G | CASE GROUND (CG) (Except H20) | |

| WIRE COLOR (22AWG) | DA 15P CONNECTOR | CHANNELS DESIGNATED IN MODEL NO. | | |
|--------------------|------------------|------------------------------------|-----|------|
| | | ABZ | ABC | ABZC |
| YEL | 13 | A | A | A |
| BLUE | 14 | B | B | B |
| ORN | 15 | Z | — | Z |
| W-YEL | 10 | — | A | A |
| W-BLU | 11 | — | B | B |
| W-OM | 12 | — | — | Z |
| RED | 6 | +V (SUPPLY VOLTAGE) | | |
| BLK | 1 | 0 V (CIRCUIT COMMON) | | |
| GRN | 9 | CASE GROUND (CG) (Except H20) | | |
| WHITE | | SHIELD DRAIN (Shielded cable only) | | |

| M18 CONNECTOR | PIN | CHANNEL |
|---------------|-----|---------|
| | A | A |
| | B | B |
| | C | Z |
| | D | +V |
| | E | — |
| | F | 0V |
| | G | — |
| | H | A |
| | I | B |
| | J | Z |

BEISENSORS

Tel: 805-968-0782 / 800-350-2727 | Fax: 805-968-3154 / 800-960-2726 | 7230 Hollister Ave., Goleta, CA 93117-2807
www.beisensors.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sensata:

[01039-1951](#) [01039-2485](#) [01039-2317](#) [01039-2635](#) [01039-2487](#) [01039-2299](#) [01039-1952](#) [01039-1979](#) [01057-133](#)
[01039-1934](#) [01039-2637](#) [01039-2834](#) [01039-2638](#) [01039-2034](#) [01039-3020](#) [01057-073](#) [01057-033](#) [01039-2221](#)
[01039-2372](#) [01039-2806](#) [01039-2814](#) [01039-1924](#) [01039-3285](#) [01039-3156](#) [01039-3229](#) [01039-2820](#) [01039-3222](#)
[01039-1998](#) [01039-2712](#) [01039-2790](#) [01039-2353](#) [01039-2259](#) [01057-046](#) [01039-2859](#) [01039-2757](#) [01039-3518](#)
[01039-3330](#) [01039-2206](#) [01039-2881](#) [01039-2886](#) [01039-2096](#) [01039-2694](#) [01039-1981](#) [01039-2630](#) [01039-](#)
[2643](#) [01057-131](#) [01039-2718](#) [01039-2631](#) [01039-2640](#) [01039-2087](#) [01039-2439](#) [01039-2731](#) [01039-3697](#) [01057-](#)
[0003](#) [01039-667](#) [01039-1984](#) [01039-2762](#) [01039-1885](#) [01039-1886](#) [01057-184](#) [01039-2624](#) [01039-2674](#) [01039-](#)
[3482](#) [01039-2677](#) [01039-1935](#) [01039-2967](#) [01039-1945](#) [01039-2947](#) [01039-2009](#) [01039-3675](#) [01039-2747](#)
[01039-2002](#) [01039-1867](#) [01039-1472](#) [01039-2071](#) [01039-1869](#) [01039-251](#) [H20-37-SS-500-ABC-28V/V-SM14-S](#)
[01039-1856](#) [01039-2154](#) [01039-3548](#) [01039-2863](#) [01039-472](#)