


Rheostats


(Potentiometers) Wirewound



MODEL C

Model Type	Watts	Ohmic range	Core	Max. Voltage (RMS)*	Behind panel "B" (in./mm)	Diameter "D" (in./mm)	Dimension "C" (in./mm)	Shaft torque	Rotation (±5°)
C RCS/RCL	7.5	10.0-5K	enclosed	305	0.875/22.23	0.515/ 13.08	—	0.25-3 oz. in.	300°


* See Catalog #203 for complete details.



MODEL E

Model Type	Watts	Ohmic range	Core	Max. Voltage (RMS)*	Behind panel "B" (in./mm)	Diameter "D" (in./mm)	Dimension "C" (in./mm)	Shaft torque	Rotation (±5°)
E RES/REL	12.5	1.0-15K	open	305	0.688/17.46	0.875/ 22.23	0.594/15.08	1-6 oz. in.	300°
E REE	12.5	1.0-15K	enclosed	305	1.219/30.96	1.047/ 26.59	—	1-6 oz. in.	300°

* See Catalog #203 for complete details.



Dimensions for reference only; consult factory for details.

Since all rheostats/potentiometers are electro-mechanical devices, they are subject to mechanical wear and, therefore, have a finite life.

Models H, J, K, L and N are listed under UL File No. E-10946 and CSA File No. 21309 unless noted otherwise.

All rheostats are 10% tolerance.

Rheostats


(Potentiometers) Wirewound

MODELS H, J, G, K, L

Model Type	Watts	Ohmic range	Core	Max. Voltage (RMS)*	Behind panel "B" (in./mm)	Diameter "D" (in./mm)	Dimension "C" (in./mm)	Shaft torque	Rotation (±5°)
H RHS/RHL	25	1.0-25K	open	500	1.375/34.93	1.560/ 39.62	0.940/23.88	0.25-0.5 lb. in.	300°
J RJS	50	0.5-50K	open	750	1.375/34.93	2.31 / 58.67	1.56 /39.62	0.25-2 lb. in.	300°
G RGS	75	0.5-50K	open	900	1.750/44.45	2.75 / 69.25	1.78 /45.21	0.5-2 lb. in.	300°
K RKS	100	0.5-50K	open	1000	1.750/44.45	3.125/ 79.38	1.91 /48.51	0.5-2 lb. in.	300°
L RLS	150	0.5-50K	open	1200	2.000 / 50.8	4.00 /101.60	2.28 /57.91	0.5-3 lb. in.	300°

* Models H, J, G, and K also available in enclosed versions.

• See Catalog #203 for complete details.



Mounting: Panels to 0.25" (6.35mm) thick with $\frac{3}{8}$ -32 bushing and hex nut ($\frac{3}{32}$ " thick) (or with 10-32 x 0.75 flat-head screws for model L only).


MODELS P, N, R, U

Model Type	Watts	Ohmic range	Core	Max. Voltage (RMS)*	Behind panel "B" (in./mm)	Diameter "D" (in./mm)	Dimension "C" (in./mm)	Shaft torque	Rotation (±5°)
P RPS	225	1.0-30K	open	1300	2.125/53.98	5.00 /127.00	2.97 /75.44	2.5-4 lb. in.	310°
N RNS	300	1.0-50K	open	1225	2.375/60.33	6.00 /152.40	3.44 /87.38	2.5-5 lb. in.	320°
R RRS	500	1.0-20K	open	1450	2.125/53.98	8.00 /203.20	4.31/109.47	4.5-7 lb. in.	325°
U RUS	1000	1.0-20K	open	1600	3.000 / 76.2	12.00 /304.80	6.38/162.05	3.5-7 lb. in.	335°

• See Catalog #203 for complete details.

Dimension "M"	
P	0.875" 22.23 mm
N	1.188" 30.16 mm
R	1.5" 38.1 mm
U	3" 76.2 mm

Mounting: Panels to 1.25" (31.75mm) thick with $\frac{1}{4}$ -20 flat-head screws.



(continued)

Rheostats

(Potentiometers) Wirewound

ORDERING INFORMATION

Code	Watts	Model	Shaft	Core
CL =	7.5	C	Locking	Enclosed
CS =	7.5	J	Standard	Enclosed
EE =	12.5	E	Locking	Open
EL =	12.5	J	Standard	Open
ES =	12.5	E	Locking	Open
GS =	75	G	Standard	Open
HL =	25	H	Locking	Open
HS =	25	J	Standard	Open
JS =	50	J	Standard	Open
KS =	100	K	Standard	Open
LS =	150	L	Standard	Open
NS =	300	N	Standard	Open
PS =	225	P	Standard	Open
RS =	500	R	Standard	Open
US =	1000	U	Standard	Open

Series —
Rheostats
Wirewound
Potentiometers

E = RoHS compliant

R C S R 5 0 E

*Check table for standard resistance values and maximum current values

Resistance Value*

Example:
R50 = 0.50Ω
1R0 = 1Ω
7R5 = 7.5Ω
250 = 250Ω
1K0 = 1,000Ω
1K75 = 1,750Ω
4K5 = 4,500Ω
50K = 50,000Ω

• RoHS compliant product available. Add "E" suffix to part number to specify.

• Made-to-order rheostats available: Contact nearest Ohmite sales office.

* Voltage rating dependent on resistance value.

Ohmic value	Part No. Prefix > Suffix <	7.5W Model C			12.5W Model E			25W Model H			50W Model J		75W Model G		100W Model K		150W Model L		225W Model P		300W Model N		500W Model R		1000W Model U		
		RCS	RCL	Amps max.	RES	REL	REE	Amps max.	RHS	RHL	Amps max.	RJS	Amps max.	RGS	Amps max.	RKS	Amps max.	RLS	Amps max.	RPS	Amps max.	RNS	Amps max.	RRS	Amps max.	RUS	Amps max.
0.5 —R50					✓	✓	✓	3.53	✓	✓	5.00	✓	10.0	✓	12.3	✓	14.1	✓	17.3	✓	15.0	✓	17.32	✓	22.3	✓	31.6
1 —1R0					✓	✓	✓	2.50	✓	✓	3.54	✓	5.00	✓	6.12	✓	7.07	✓	8.65	✓	10.6	✓	12.24	✓	15.8	✓	25.8
1.5 —1R5					✓	✓	✓	2.24	✓	✓													✓	14.1	✓	22.4	
2 —2R0					✓	✓	✓	2.04	✓	✓	2.88			✓	5.00	✓	5.75	✓	7.07	✓	8.66	✓	10.00	✓	12.9	✓	18.3
2.5 —2R5					✓	✓	✓	1.58	✓	✓	2.04	✓	2.88	✓	3.88	✓	4.47	✓	5.48	✓	6.71	✓	7.75	✓	11.2	✓	15.8
3 —3R0					✓	✓	✓	1.44	✓	✓				✓	3.16	✓	3.65	✓	4.47	✓	5.49	✓	6.32	✓	10.0	✓	14.1
4 —4R0					✓	✓	✓	1.25	✓	✓	1.77	✓	2.50	✓	2.74	✓	3.16	✓	3.88	✓	4.74	✓	5.48	✓	7.90	✓	11.2
5 —5R0					✓	✓	✓	1.12	✓	✓	1.58	✓	2.04											✓	10.0	✓	10.0
6 —6R0					✓	✓	✓	0.91	✓	✓	1.29			✓	2.17	✓	2.50	✓	3.163	✓	3.87	✓	4.47	✓	6.30	✓	8.95
7.5 —7R5					✓	✓	✓	0.71	✓	✓				✓	1.73	✓	2.0	✓	2.450	✓	3.00	✓	3.46	✓	4.47	✓	6.33
8 —8R0	✓	✓	0.86		✓	✓	✓	0.71	✓	✓	1.00	✓	1.19	✓	1.73	✓	2.0	✓	2.450	✓	3.00	✓	3.46	✓	4.47	✓	6.33
10 —10R	✓	✓	0.71		✓	✓	✓	0.60	✓	✓	0.845	✓	1.19	✓	1.73	✓	2.0	✓	2.450	✓	3.00	✓	3.46	✓	4.47	✓	6.33
12 —12R					✓	✓	✓	0.50	✓	✓	0.707	✓	1.00	✓	1.23	✓	1.41	✓	1.735	✓	2.12	✓	2.45	✓	3.16	✓	4.47
12.5 —12R5					✓	✓	✓	0.40	✓	✓	0.575	✓	0.790	✓	1.00	✓	1.15	✓	1.415	✓	1.73	✓	2.00	✓	2.52	✓	3.65
15 —15R	✓	✓	0.71		✓	✓	✓	0.36	✓	✓	0.500	✓	0.630	✓	0.866	✓	1.00	✓	1.225	✓	1.50	✓	1.73	✓	2.00	✓	3.16
16 —16R					✓	✓	✓	0.29	✓	✓	0.375	✓	0.575					✓	1.000	✓	1.22	✓	1.41			✓	2.39
22 —22R					✓	✓	✓	0.25	✓	✓		✓	0.470	✓	0.612	✓	0.707	✓	0.865	✓	1.06	✓	1.22	✓	1.69	✓	2.11
25 —25R	✓	✓	0.55		✓	✓	✓	0.19	✓	✓	0.222	✓	0.316	✓	0.433	✓	0.500	✓	0.655	✓	0.750	✓	0.866	✓	1.00	✓	1.48
35 —35R	✓	✓	0.46		✓	✓	✓	0.16	✓	✓	0.222	✓	0.316	✓	0.388	✓	0.447	✓	0.548	✓	0.567	✓	0.655	✓	0.817	✓	1.15
40 —40R					✓	✓	✓	0.13	✓	✓	0.182	✓	0.250	✓	0.316	✓	0.365	✓	0.447	✓	0.567	✓	0.655	✓	0.817	✓	1.15
50 —50R	✓	✓	0.39		✓	✓	✓	0.10	✓	✓	0.155	✓	0.224	✓	0.274	✓	0.316	✓	0.388	✓	0.447	✓	0.500	✓	0.578	✓	0.707
75 —75R	✓	✓	0.32		✓	✓	✓	0.090	✓	✓	0.129			✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
80 —80R					✓	✓	✓	0.071	✓	✓		✓	0.176					✓	0.346	✓	0.387	✓	0.447	✓	0.500	✓	0.633
100 —100	✓	✓	0.27		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
125 —125	✓	✓	0.22		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
150 —150	✓	✓	0.22		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
160 —160					✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
175 —175	✓	✓	0.19		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
200 —200	✓	✓	0.19		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
225 —225	✓	✓	0.17		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
250 —250	✓	✓	0.17		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
300 —300	✓	✓	0.15		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
325 —325	✓	✓	0.15		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
350 —350	✓	✓	0.15		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
400 —400	✓	✓	0.12		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
500 —500	✓	✓	0.12		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
600 —600	✓	✓	0.10		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
700 —700	✓	✓	0.10		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
750 —750	✓	✓	0.10		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
800 —800	✓	✓	0.10		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
900 —900	✓	✓	0.086		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
1000 —1K0	✓	✓	0.086		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
1200 —1K2	✓	✓	0.071		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
1250 —1K25	✓	✓	0.071		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
1500 —1K5	✓	✓	0.071		✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
1600 —1K6					✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
1750 —1K75					✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
1800 —1K8					✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
2000 —2K0					✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
2250 —2K25					✓	✓	✓	0.071	✓	✓				✓	0.224	✓	0.258	✓	0.316	✓	0.387	✓	0.447	✓	0.500	✓	0.633
2500 —2K5	✓	✓	0.055		✓	✓	✓	0.070	✓	✓	0.100	✓	0.141	✓	0.173	✓	0.200	✓	0.224	✓	0.300	✓	0.346	✓	0.447	✓	0.633
3000 —3K0	✓	✓	0.046		✓	✓	✓	0.060	✓	✓	0.084	✓	0.119	✓	0.141	✓	0.161	✓	0.182	✓	0.300	✓	0.346	✓	0.447		