

**JUMO GmbH & Co. KG**  
 Delivery address: Mackenrodtstraße 14,  
 36039 Fulda, Germany  
 Postal address: 36035 Fulda, Germany  
 Phone: +49 661 6003-0  
 Fax: +49 661 6003-607  
 e-mail: mail@jumo.net  
 Internet: www.jumo.net

**JUMO Instrument Co. Ltd.**  
 JUMO House  
 Temple Bank, Riverway  
 Harlow, Essex CM20 2DY, UK  
 Phone: +44 1279 635533  
 Fax: +44 1279 635262  
 e-mail: sales@jumo.co.uk  
 Internet: www.jumo.co.uk

**JUMO Process Control, Inc.**  
 8 Technology Boulevard  
 Canastota, NY 13032, USA  
 Phone: 315-697-JUMO  
 1-800-554-JUMO  
 Fax: 315-697-5867  
 e-mail: info@jumo.us  
 Internet: www.jumo.us



## JUMO LOGOSCREEN nt

# Paperless recorder with TFT display, CompactFlash card and USB interfaces

## Brief description

The LOGOSCREEN nt represents a new generation of paperless recorders from JUMO that stand out through their modular design for the acquisition of measurement data (3 to 18 measurement inputs can be implemented internally), their innovative operating concept and high standards of security to prevent unauthorized access and manipulation of the stored data.

In the LOGOSCREEN nt, data can be visualized in process images as measurement curves, as a bar graph or in alphanumerical form.

Powerful PC programs are available for analyzing and evaluating the archived data, and for configuring the LOGOSCREEN nt.

## Block structure

### Inputs/Outputs

0...18 analog inputs max.  
 0...24 binary inputs/outputs max.

(maximum of 3 module slots,  
 can be fitted with 6 analog inputs  
 or 3 analog inputs  
 and 8 binary inputs/outputs)

### Inputs via interface

additionally  
 up to 24 analog inputs and  
 up to 24 binary inputs

### Relay outputs

1 relay (standard)  
 additionally  
 6 relays (option)

### Display/Operation

**Display**  
 5.5" TFT color display,  
 320 x 240 pixels,  
 256 colors

**Operation**  
 rotary knob or touchpad  
 (left, right, press)

**JUMO LOGOSCREEN nt**

### Power supply

AC 100...240V +10/-15%,  
 48...63Hz  
 AC/DC 20...30V, 48...63Hz (ELV)

### Interface

as standard  
 1x Ethernet 10/100 Mbits/sec  
 4x USB interfaces  
 1x RS232/RS485  
 1x RS232 (barcode reader)  
 option:  
 1x PROFIBUS-DP

### Meas. data memory

internal memory  
 256 Mbytes  
 external memory  
 CompactFlash card and  
 USB memory stick

### Internal channels

18x math channels  
 18x logic channels  
 27x counters / integrators

### Software

Setup program  
 PC Eval. software (PCA3000)  
 PCA Communications software



Type 706581/...



Type 706581/...,444  
 (Stainless steel front )

## Key features

- Easy operation by control knob or touchpad
- Measurement data storage on CompactFlash memory card or USB memory stick
- Automatic read-out of data through the PCA Communications Software (PCC)
- Interface to SCADA systems, to PLC controls and PC systems
- Integrated web server
- Simultaneous recording of up to 3 batch reports
- Batch control (start, stop, texts) through barcode reader
- Modbus master function
- ATEX approval with stainless steel front

 II 2G Ex px IIC

 II 2D Ex pD 21 IP65

## Approvals/marks of conformity (see Technical data)



## Technical data

### Analog inputs

#### Thermocouple

| Designation                          | Type                                                                                                          | Standard          | Meas. range     | Accuracy <sup>1</sup> |
|--------------------------------------|---------------------------------------------------------------------------------------------------------------|-------------------|-----------------|-----------------------|
| Fe-CuNi                              | L                                                                                                             | DIN 43 710        | -200 to +900°C  | ±0.1 %                |
| Fe-CuNi                              | J                                                                                                             | EN 60 584         | -200 to +1200°C | ±0.1 % from -100°C    |
| Cu-CuNi                              | U                                                                                                             | DIN 43 710        | -200 to +600°C  | ±0.1 % from -150°C    |
| Cu-CuNi                              | T                                                                                                             | EN 60 584         | -270 to +400°C  | ±0.1 % from -150°C    |
| NiCr-Ni                              | K                                                                                                             | EN 60 584         | -200 to +1372°C | ±0.1 % from -80°C     |
| NiCr-CuNi                            | E                                                                                                             | EN 60 584         | -200 to +1000°C | ±0.1 % from -80°C     |
| NiCrSi-NiSi                          | N                                                                                                             | EN 60 584         | -100 to +1300°C | ±0.1 % from -80°C     |
| Pt10Rh-Pt                            | S                                                                                                             | EN 60 584         | 0 to 1768°C     | ±0.15 %               |
| Pt13Rh-Pt                            | R                                                                                                             | EN 60 584         | 0 to 1768°C     | ±0.15 %               |
| Pt30Rh-Pt6Rh                         | B                                                                                                             | EN 60 584         | 0 to 1820°C     | ±0.15 % from 400°C    |
| W3Re/W25Re                           | D                                                                                                             |                   | 0 to 2495°C     | ±0.15 % from 500°C    |
| W5Re/W26Re                           | C                                                                                                             |                   | 0 to 2320°C     | ±0.15 % from 500°C    |
| W3Re/W26Re                           |                                                                                                               |                   | 0 to 2400°C     | ±0.15 % from 500°C    |
| Chromel-copel                        |                                                                                                               | GOST R 8.585-2001 | -200 to +800°C  | ±0.15 % from -80°C    |
| Chromel-alumel                       |                                                                                                               | GOST R 8.585-2001 | -200 to +1372°C | ±0.1 % from -80°C     |
| PLII (Platinel II)                   |                                                                                                               |                   | 0 to 1395°C     | ±0.15 %               |
| Shortest span                        | Type L, J, U, T, K, E, N, chromel-alumel, PLII: 100°C<br>Type S, R, B, D, C, W3Re/W26Re, chromel-copel: 500°C |                   |                 |                       |
| Range start/end                      | freely programmable within the limits, in 0.1°C steps                                                         |                   |                 |                       |
| Cold junction                        | Pt100 internal or thermostat external constant                                                                |                   |                 |                       |
| Cold junction accuracy (internal)    | ± 1°C                                                                                                         |                   |                 |                       |
| Cold junction temperature (external) | -50 to +150°C adjustable                                                                                      |                   |                 |                       |
| Sampling cycle                       | Channel 1 - 18: 125ms in total                                                                                |                   |                 |                       |
| Input filter                         | 2nd order digital filter; filter constant adjustable from 0 to 10.0 sec                                       |                   |                 |                       |
| Electrical isolation                 | see "Electrical data" on page 5 and<br>"Overview of the electrical isolation" on page 16                      |                   |                 |                       |
| Resolution                           | > 14 bit                                                                                                      |                   |                 |                       |
| Features                             | also programmable in °F                                                                                       |                   |                 |                       |

<sup>1</sup> The linearization accuracy refers to the maximum measuring range. The linearization accuracy is reduced with short spans.

#### Resistance thermometer

| Designation | Standard                                                                     | Connection circuit | Meas. range     | Accuracy <sup>1</sup> | Meas. curr. |
|-------------|------------------------------------------------------------------------------|--------------------|-----------------|-----------------------|-------------|
| Pt100       | EN 60 751<br>(TC = $3.85 \cdot 10^{-3} \text{ } 1/^{\circ}\text{C}$ )        | 2/3-wire           | -200 to +100°C  | ±0.5°C                | ≈ 250µA     |
|             |                                                                              | 2/3-wire           | -200 to +850°C  | ±0.8°C                | ≈ 250µA     |
|             |                                                                              | 4-wire             | -200 to +850°C  | ±0.5°C                | ≈ 250µA     |
| Pt100       | JIS 1604<br>(TC = $3.917 \cdot 10^{-3} \text{ } 1/^{\circ}\text{C}$ )        | 2/3-wire           | -200 to +100°C  | ±0.5°C                | ≈ 250µA     |
|             |                                                                              | 2/3-wire           | -200 to +650°C  | ±0.8°C                | ≈ 250µA     |
|             |                                                                              | 4-wire             | -200 to +650°C  | ±0.5°C                | ≈ 250µA     |
| Pt100       | GOST 6651-94 A.1<br>(TC = $3.91 \cdot 10^{-3} \text{ } 1/^{\circ}\text{C}$ ) | 2/3-wire, 4-wire   | -200 to +100°C  | ±0.5°C                | ≈ 250µA     |
|             |                                                                              | 2/3-wire, 4-wire   | -200 to +850°C  | ±0.8°C                | ≈ 250µA     |
| Pt500       | EN 60 751<br>(TC = $3.85 \cdot 10^{-3} \text{ } 1/^{\circ}\text{C}$ )        | 2/3-wire, 4-wire   | -200 to +100°C  | ±0.5°C                | ≈ 100µA     |
|             |                                                                              | 2/3-wire, 4-wire   | -200 to +850°C  | ±0.9°C                | ≈ 100µA     |
| Pt1000      | EN 60 751<br>(TC = $3.85 \cdot 10^{-3} \text{ } 1/^{\circ}\text{C}$ )        | 2/3-wire           | -200 to +100°C  | ±0.5°C                | ≈ 100µA     |
|             |                                                                              | 2/3-wire           | -200 to +850°C  | ±0.8°C                | ≈ 100µA     |
|             |                                                                              | 4-wire             | -200 to +850°C  | ±0.5°C                | ≈ 100µA     |
| Ni 100      | DIN 43 760<br>(TC = $6.18 \cdot 10^{-3} \text{ } 1/^{\circ}\text{C}$ )       | 2/3-wire, 4-wire   | -60 to +180°C   | ±0.4°C                | ≈ 250µA     |
| Pt50        | ST RGW 1057 1985<br>(TC = $3.91 \cdot 10^{-3} \text{ } 1/^{\circ}\text{C}$ ) | 2/3-wire           | -200 to +100°C  | ±0.5°C                | ≈ 250µA     |
|             |                                                                              | 2/3-wire           | -200 to +1100°C | ±0.9°C                | ≈ 250µA     |
|             |                                                                              | 4-wire             | -200 to +100°C  | ±0.5°C                | ≈ 250µA     |
|             |                                                                              | 4-wire             | -200 to +1100°C | ±0.6°C                | ≈ 250µA     |
| Cu 50       | (TC = $4.26 \cdot 10^{-3} \text{ } 1/^{\circ}\text{C}$ )                     | 2/3-wire           | -50 to +100°C   | ±0.5°C                | ≈ 250µA     |
|             |                                                                              | 2/3-wire           | -50 to +200°C   | ±0.9°C                | ≈ 250µA     |
|             |                                                                              | 4-wire             | -50 to +100°C   | ±0.5°C                | ≈ 250µA     |
|             |                                                                              | 4-wire             | -50 to +200°C   | ±0.7°C                | ≈ 250µA     |

| Designation            | Standard                                                                                    | Connection circuit                       | Meas. range                                                      | Accuracy <sup>1</sup>                                                                                    | Meas. curr.                                                                                                  |
|------------------------|---------------------------------------------------------------------------------------------|------------------------------------------|------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|
| Cu 100                 | GOST 6651-94 A.4<br>(TC = $4.26 \cdot 10^{-3} \text{ 1/}^\circ\text{C}$ )                   | 2/3-wire<br>2/3-wire<br>4-wire<br>4-wire | -50 to +100°C<br>-50 to +200°C<br>-50 to +100°C<br>-50 to +200°C | $\pm 0.5^\circ\text{C}$<br>$\pm 0.9^\circ\text{C}$<br>$\pm 0.5^\circ\text{C}$<br>$\pm 0.6^\circ\text{C}$ | $\approx 250\mu\text{A}$<br>$\approx 250\mu\text{A}$<br>$\approx 250\mu\text{A}$<br>$\approx 250\mu\text{A}$ |
| Connection circuit     | 2-, 3-, or 4-wire circuit                                                                   |                                          |                                                                  |                                                                                                          |                                                                                                              |
| Shortest span          | 15°C                                                                                        |                                          |                                                                  |                                                                                                          |                                                                                                              |
| Sensor lead resistance | max. 30 per conductor for 3-wire/4-wire circuit<br>max. 10 per conductor for 2-wire circuit |                                          |                                                                  |                                                                                                          |                                                                                                              |
| Range start/end        | freely programmable within the limits, in 0.1°C steps                                       |                                          |                                                                  |                                                                                                          |                                                                                                              |
| Sampling cycle         | Channel 1 - 18: 125ms in total                                                              |                                          |                                                                  |                                                                                                          |                                                                                                              |
| Input filter           | 2nd order digital filter; filter constant adjustable from 0 to 10 sec                       |                                          |                                                                  |                                                                                                          |                                                                                                              |
| Electrical isolation   | see "Electrical data" on page 5 and<br>"Overview of the electrical isolation" on page 16    |                                          |                                                                  |                                                                                                          |                                                                                                              |
| Resolution             | >14 bit                                                                                     |                                          |                                                                  |                                                                                                          |                                                                                                              |
| Features               | also programmable in °F                                                                     |                                          |                                                                  |                                                                                                          |                                                                                                              |

<sup>1</sup> The linearization accuracy refers to the maximum measuring range. The linearization accuracy is reduced with short spans.

#### Resistance transmitter and potentiometer

| Designation            | Meas. range                                                                              | Accuracy <sup>1</sup>                    | Meas. curr.                                          |
|------------------------|------------------------------------------------------------------------------------------|------------------------------------------|------------------------------------------------------|
| Resistance transmitter | up to 4000Ω                                                                              | $\pm 4\Omega$                            | $\approx 100\mu\text{A}$                             |
| Potentiometer          | < 400Ω<br>≥ 400Ω to 4000Ω                                                                | $\pm 400\text{m}\Omega$<br>$\pm 4\Omega$ | $\approx 250\mu\text{A}$<br>$\approx 100\mu\text{A}$ |
| Connection circuit     | resistance transmitter: 3-wire circuit<br>potentiometer: 2-/3-/4-wire circuit            |                                          |                                                      |
| Shortest span          | 60Ω                                                                                      |                                          |                                                      |
| Sensor lead resistance | max. 30 per conductor for 4-wire circuit<br>max. 10 per conductor for 2-/3-wire circuit  |                                          |                                                      |
| Resistance values      | freely programmable within the limits, in 0.1 steps                                      |                                          |                                                      |
| Sampling cycle         | Channel 1 - 18: 125ms in total                                                           |                                          |                                                      |
| Input filter           | 2nd order digital filter; filter constant adjustable from 0 to 10.0 sec                  |                                          |                                                      |
| Electrical isolation   | see "Electrical data" on page 5 and<br>"Overview of the electrical isolation" on page 16 |                                          |                                                      |
| Resolution             | >14 bit                                                                                  |                                          |                                                      |

<sup>1</sup> The linearization accuracy refers to the maximum measuring range. The linearization accuracy is reduced with short spans.

#### Input for DC voltage, DC current

| Basic range                                                                                             | Accuracy <sup>1</sup>                                                                                                         | Input resistance                                                                                                                                                                           |
|---------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| -12 to +112mV<br>-10 to +210mV<br>-1.5 to +11.5V<br>-0.12 to +1.12V<br>-1.2 to +1.2V<br>-11.2 to +11.2V | $\pm 100\mu\text{V}$<br>$\pm 240\mu\text{V}$<br>$\pm 6\text{mV}$<br>$\pm 1\text{mV}$<br>$\pm 2\text{mV}$<br>$\pm 12\text{mV}$ | $R_E \geq 1\text{M}\Omega$<br>$R_E \geq 470\text{k}\Omega$<br>$R_E \geq 470\text{k}\Omega$<br>$R_E \geq 470\text{k}\Omega$<br>$R_E \geq 470\text{k}\Omega$<br>$R_E \geq 470\text{k}\Omega$ |
| Shortest span                                                                                           | 5mV                                                                                                                           |                                                                                                                                                                                            |
| Range start/end                                                                                         | freely programmable within the limits in 0.01 mV steps                                                                        |                                                                                                                                                                                            |
| -1.3 to +22mA<br>-22 to +22mA                                                                           | $\pm 20\mu\text{A}$<br>$\pm 44\mu\text{A}$                                                                                    | burden voltage ≤ 3V<br>burden voltage ≤ 3V                                                                                                                                                 |
| Shortest span                                                                                           | 0.5mA                                                                                                                         |                                                                                                                                                                                            |
| Range start/end                                                                                         | freely programmable within the limits in 0.01 mA steps                                                                        |                                                                                                                                                                                            |
| Overrange/underrange                                                                                    | according to NAMUR NE 43                                                                                                      |                                                                                                                                                                                            |
| Sampling cycle                                                                                          | Channel 1 - 18: 125ms in total                                                                                                |                                                                                                                                                                                            |
| Input filter                                                                                            | 2nd order digital filter; filter constant adjustable from 0 to 10.0 sec                                                       |                                                                                                                                                                                            |
| Electrical isolation                                                                                    | see "Electrical data" on page 5 and<br>"Overview of the electrical isolation" on page 16                                      |                                                                                                                                                                                            |
| Resolution                                                                                              | >14 bit                                                                                                                       |                                                                                                                                                                                            |

<sup>1</sup> The linearization accuracy refers to the maximum measuring range. The linearization accuracy is reduced with short spans.

**Transducer short circuit/break**

|                                 | <b>Short-circuit<sup>1</sup></b> | <b>Break<sup>1</sup></b> |
|---------------------------------|----------------------------------|--------------------------|
| Thermocouple                    | not detected                     | detected                 |
| Resistance thermometer          | detected                         | detected                 |
| Resistance transmitter          | not detected                     | detected                 |
| Potentiometer                   | not detected                     | detected                 |
| Voltage $\leq \pm 210\text{mV}$ | not detected                     | detected                 |
| Voltage $> \pm 210\text{mV}$    | not detected                     | not detected             |
| Current                         | not detected                     | not detected             |

<sup>1</sup> Programmable reaction of device, e.g. triggering alarm

**Binary inputs/outputs (option)**

|                      |                                                                                                                                                                                                                                              |
|----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Input or output      | configurable as input or output                                                                                                                                                                                                              |
| Number               | 8, 16 or 24, depending on the device version,<br>to DIN VDE 0411, Part 500; max. 25Hz, max. 32V                                                                                                                                              |
| Input                |                                                                                                                                                                                                                                              |
| - level              | logic "0": -3 to +5V (input current max. $\pm 1\text{mA}$ ),<br>logic "1": 12 to 30V ( $2.5\text{mA} \leq \text{input current} \leq 5\text{mA}$ )                                                                                            |
| - counting frequency | 8Hz                                                                                                                                                                                                                                          |
| High-speed input     | the first two binary inputs of each module (B1, B2, B9, B10, B17, B18),<br>if the module is not fitted with relays or 6 analog inputs                                                                                                        |
| - task               | count function, e.g. for flow measurement                                                                                                                                                                                                    |
| - counting frequency | 10kHz                                                                                                                                                                                                                                        |
| Output               |                                                                                                                                                                                                                                              |
| - type               | open-collector output, switches relative to positive voltage                                                                                                                                                                                 |
| - level              | logic "0": transistor is inhibited<br>(max. permissible voltage across switching transistor 30V, max. leakage current 0.1 mA)<br>logic "1": transistor is switched on<br>(max. voltage across switching transistor 1.6V, max. current 50 mA) |
| - sampling cycle     | at least 1 sec (1 Hz)                                                                                                                                                                                                                        |

**Outputs**

|                      |                                               |
|----------------------|-----------------------------------------------|
| 1 relay (ex-factory) | changeover (SPDT), 3A, 230V AC <sup>1</sup>   |
| 6 relays (option)    | changeover (SPDT), 3A, 230V AC <sup>1,2</sup> |

<sup>1</sup> With resistive load. <sup>2</sup> It is not permissible to mix SELV circuits and supply circuits.

**Interfaces**

|                                        |                                                                                          |
|----------------------------------------|------------------------------------------------------------------------------------------|
| RS232/RS485 (connector 7)              |                                                                                          |
| - protocol                             | Qty. 1, switchable between RS232 and RS485                                               |
| - baud rate                            | Modbus master, Modbus slave and barcode reader                                           |
| - modem                                | 9600, 19200, 38400                                                                       |
| - connector                            | can be connected                                                                         |
| - external inputs                      | SUB-D                                                                                    |
|                                        | via the Modbus master/slave function, 24 analog and 24 binary                            |
| RS232 for barcode reader (connector 2) |                                                                                          |
| - protocol                             | Qty. 1                                                                                   |
| - baud rate                            | Modbus master, Modbus slave and barcode reader                                           |
| - connector                            | 9600, 19200, 38400                                                                       |
| - external inputs                      | SUB-D                                                                                    |
|                                        | via the Modbus master/slave function, 24 analog and 24 binary                            |
| Ethernet (connector 6)                 |                                                                                          |
| - quantity                             | max. 1                                                                                   |
| - protocols                            | TCP, IP, HTTP, DHCP, SMTP, ModbusTCP                                                     |
| - baud rate                            | 10Mbits/sec, 100Mbits/sec                                                                |
| - connector                            | RJ45                                                                                     |
| - data format                          | HTML                                                                                     |
| USB host (connector 5)                 |                                                                                          |
| - quantity                             | 2 (or 1 with stainless steel front),                                                     |
| - use                                  | connector 5 and front connector (not with stainless steel front); no parallel operation  |
| - max. current                         | for connecting a memory stick                                                            |
|                                        | 100mA                                                                                    |
| USB device (connector 15)              |                                                                                          |
| - quantity                             | 2 (or 1 with stainless steel front),                                                     |
| - use                                  | connector 15 and front connector (not with stainless steel front); no parallel operation |
|                                        | for connecting to the (master) computer                                                  |

**Screen**

|                           |                                        |
|---------------------------|----------------------------------------|
| Resolution / size         | 320 x 240 pixels / 5.5"                |
| Type / number of colors   | TFT color screen / 256 colors          |
| Screen refresh rate       | > 150Hz                                |
| Brightness setting        | adjustable on instrument               |
| Screen saver (switch-off) | through waiting time or control signal |

**Electrical data**

|                                                                   |                                                                                                                                                            |
|-------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Supply voltage (switch-mode PSU)                                  | 100 - 240V AC +10/-15 %, 48 - 63Hz or 20 - 30V AC/DC, 48 - 63Hz (ELV)                                                                                      |
| Electrical safety                                                 | to EN 61 010, Part 1, August 2002<br>overvoltage category II, pollution degree 2<br>terminal for PE conductor                                              |
| Protection class I                                                |                                                                                                                                                            |
| Test voltages (type test)                                         |                                                                                                                                                            |
| - mains supply circuit to meas. circuit                           | with AC supply: 2.3kV/50Hz, 1 min,<br>with AC/DC supply: 2.3kV/50Hz, 1 min                                                                                 |
| - mains supply circuit to housing (protective conductor)          | with AC supply: 2.3kV/50Hz, 1 min,<br>with AC/DC supply: 2.3kV/50Hz, 1 min                                                                                 |
| - measuring current circuits to meas. current circuit and housing | 500V/50Hz, 1 min                                                                                                                                           |
| - electrical isolation between analog inputs                      | up to 30V AC and 50V DC                                                                                                                                    |
| Supply voltage error                                              | < 0.1 % of range span                                                                                                                                      |
| Power consumption                                                 | approx. 40VA                                                                                                                                               |
| Data backup                                                       | CompactFlash memory card                                                                                                                                   |
| Electrical connection                                             |                                                                                                                                                            |
| - mains supply and relays                                         | at rear through pluggable screw terminals, 5.08mm raster,<br>max. conductor cross-section $\leq 2.5\text{mm}^2$ or $2 \times 1.5\text{mm}^2$ with ferrules |
| - analog and binary inputs                                        | at rear through pluggable screw terminals, 3.81mm raster,<br>max. conductor cross-section $\leq 1.5\text{mm}^2$                                            |

**Environmental influences**

|                            |                                                |
|----------------------------|------------------------------------------------|
| Ambient temperature range  | 0 to +50°C                                     |
| Ambient temperature effect | 0.03 %/°C                                      |
| Storage temperature range  | -20 to +60°C                                   |
| Climatic conditions        | $\leq 75\%$ relative humidity, no condensation |
| EMC                        | EN 61 326-1                                    |
| - interference emission    | Class A - only for industrial use -            |
| - immunity to interference | to industrial requirements                     |

**Housing**

|                      |                                                                                                                                               |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Housing front        | zinc die-casting, optionally in stainless steel (extra code)                                                                                  |
| Housing type         | housing for flush-panel mounting to IEC 61 554, in stainless steel                                                                            |
| Bezel size           | 144mm x 144mm to IEC 61 554                                                                                                                   |
| Depth behind panel   | 193mm (incl. terminals)                                                                                                                       |
| Panel cut-out        | $138^{+1.0}\text{mm} \times 138^{+1.0}\text{mm}$ to IEC 61 554                                                                                |
| Panel thickness      | 2 - 40mm                                                                                                                                      |
| Housing mounting     | in panel to DIN 43 834                                                                                                                        |
| Operating position   | unrestricted, but taking into account the viewing angle of the screen,<br>horizontally $\pm 65^\circ$ , vertically $+40^\circ$ to $-65^\circ$ |
| Enclosure protection | to EN 60 529 Category 2, front IP65, rear IP20                                                                                                |
| Weight               | approx. 3.5kg                                                                                                                                 |

**Approvals/marks of conformity**

| Mark of conformity                     | Testing laboratory        | Certificates / certification numbers | Test basis                                                                                 | valid for                                                                                           |
|----------------------------------------|---------------------------|--------------------------------------|--------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|
| c UL us                                | Underwriters Laboratories | E 201387                             | UL 61010-1<br>CAN/CSA-C22.2 No. 61010-1                                                    | the flush-mounted instrument;<br>not in conjunction with extra code 350                             |
| II 2G Ex px IIC<br>II 2D Ex pD 21 IP65 | electrosuisse             | SEV 08 ATEX 0155 U                   | EN 1127-1:2007<br>EN 60079-0:2006<br>EN 60079-2:2007<br>EN 61241-0:2006<br>EN 61241-4:2006 | the flush-mounted instrument;<br>only in conjunction with extra code 444 and without extra code 350 |



Control knob, to rotate and press.

CompactFlash memory card and USB interfaces behind housing door.

## Instrument description

### Hardware

The paperless recorder is built to a modular design. The basic type consists of a PSU board (incl. relays) and a CPU board (incl. Ethernet and RS232/RS485 interfaces and an RS232 interface for barcode reader and USB interface connection).

Module slots 1, 2 and 3 can be fitted with input modules, each with 6 analog inputs or 3 analog inputs and 8 binary inputs/outputs. Alternatively, module slot 3 can be fitted with a relay module that has 6 relays. Optionally, the PSU board can be equipped with a PROFIBUS-DP interface.

### Data recording

Measurements are acquired continuously in a 125msec sampling cycle. Based on these measurements, reports are compiled and limits checked.

The measurements are transferred to the main memory of the instrument, according to the programmable storage cycle and stored value (maximum, minimum, average, min&max, instantaneous value or economy mode).

The paperless recorder saves the data in groups, and an input can be assigned to several groups (maximum 9).

### Main memory (SRAM)

The data stored in the SRAM are regularly copied to the internal memory in 20 kbyte blocks.

### Internal memory

When a block in the main memory has been filled, it is copied to the internal memory. The internal memory has a capacity of max. 256 Mbytes.

Every write action is monitored, so that any errors in saving the data can be immediately identified.

The instrument monitors the capacity of the internal memory and activates one of

the "memory alarm" signals when the capacity falls below the configurable residual capacity level. These signals can be used, for instance, to operate the alarm relay.

The memory is written as a ring memory, i. e. when the memory is full, the oldest data are automatically overwritten by the new data.

Data from the internal memory can be shown as a history presentation on the recorder. The size of the history memory can be configured.

### Data transfer to the PC

Data transfer from the paperless recorder to a PC is made by means of the external CompactFlash memory card (not available with stainless steel front), the USB memory stick or via one of the interfaces (USB device, RS232, RS485, Ethernet).

### Data security

The data are stored in coded form in a proprietary format. This ensures a high level of data security.

If the paperless recorder is disconnected from the supply, then:

- RAM and clock time are buffered by a lithium battery (ex-factory)  $\geq 10$  years or with a storage capacitor  $\geq 2$  days (ambient temperature  $-40$  to  $+45$  °C),
- measurement and configuration data in the internal memory will not be lost.

### Recording duration

Depending on the configuration of the instrument, the duration of the recording can vary over a considerable range (from a few days up to several months).

### Report

For each channel of a group, a report (maximum/minimum/average or integrator) can be run over defined periods.

### Batch reports

Up to three batch reports can be created simultaneously in the recorder. The measurement data, start, end and duration of each batch can be displayed together with a batch counter and freely definable texts, both on the recorder and within the PC Evaluation Software PCA3000.

On request, a barcode reader can be used to start batches and read in batch texts.

## Limit checkline

### changeover of operating mode

Over/underlimit conditions trigger alarms. An alarm can be used, for instance, as a control signal for changing over the operating mode.

The storage cycle and stored value can be configured separately for all three operating modes.

With the help of the alarm delay function, brief occurrences or over/underlimit conditions can be filtered out, with the result that no alarm is generated.

### Normal operation

If the instrument is **not** in timed or event operation, normal operation is active.

### Event operation

Event operation is activated/deactivated by a control signal (binary input, group/combination alarm, ...). As long as the control signal is active, the instrument is in event operation.

### Timed operation

Timed operation is active on a daily basis within a programmable time period. The operating modes have different priorities.

## Counters/integrators

27 additional internal channels are available for use as counters, integrators, operating time counters or for flow measurements.

These counters are controlled through the binary inputs, the alarms, or via the logic channels. The analog channels can be used for the integrators.

The numerical indication is shown in a separate window, with a maximum of 9 digits. The acquisition period can be selected as: periodic, daily, weekly, monthly, yearly as well as external, total (overall count) or daily from ... to.

A maximum of 6 binary inputs are available as high-speed counters with a 10 kHz sampling cycle rate.

## Math/logic module (extra code)

The module for math and logic (18 channels each) enables, for instance, the combination of analog channels with one another, and also the combination of analog channels with counters and binary inputs. The operators available for formulae are: +, -, \*, /, SQRT(), MIN(), MAX(), SIN(), COS(), TAN(), \*\*, EXP(), ABS(), INT(), FRC(), LOG(), LN(), humidity, moving average or !, &, |, ^, as well as ( and ).

The math and logic module can only be configured through the setup program.

## Operation and configuration

### On the recorder

The instrument is configured from the control knob (or with stainless steel front, from the touchpad) on the front panel under menu guidance.

-  Shift current menu position (cursor) to the left or upwards.
-  Shift current menu position (cursor) to the right or downwards.
-  When the control knob is pressed, the current function is executed.

Example:




-  Rotate control knob to the left.




-  Press control knob.

Result: The menu for the alarm and event list is called up.



-  Rotate control knob to the left.



-  Press control knob.

Result: The menu for the alarm and event list is closed again.




 Integrated user lists (different users with different authorizations) protect the recorder against unauthorized access.

### Through the setup program

As an alternative to the configuration from the control knob on the recorder, the instrument can also be configured through the setup program.

Communication between the setup program and the paperless recorder is made through the:

- USB device interface,
- serial interface,
- Ethernet interface,
- CompactFlash memory card or
- USB memory stick.



The configuration data can be archived on a data storage medium and output to the printer.

## Operating language

Two languages (see order details) are integrated in the instrument ex-factory. The setup program is used to exchange the operator language.

The languages available at the moment are: English, French, German, Russian, Japanese, Chinese, Italian, Romanian, Czech, Hungarian, Polish and Greek. Other language versions (with Unicode capability) can be created.

## Web server

The web server is integrated in the paperless recorder as standard. Four different modes of presentation are available:


- online visualization
- three freely programmable HTML pages
- current batch reports
- 4-way view (1 to 4 recorders or different visualizations)



On the PC side, the web server can be addressed with the (Microsoft®) Internet Explorer. For visualizing graphics, an SVG Viewer (from Adobe®, for instance) must be installed on the PC in addition to the Internet Explorer.

## Process images (editor)

The setup program can create process images and transfer them to the paperless recorder for display. Up to 25 objects (images, analog channels, binary channels, texts, ...) can be used in a process image.




One process image is integrated in the paperless recorder ex-factory.




## Visualization on the instrument

### Operator level




- Selection of visualization

### Vertical diagram




- Recorder chart presentation of analog and binary channels
- Display of scaling and limit markers of a channel (can be switched on/off)
- Numerical display of current analog channels

### Bar graph presentation




- Bar graph presentation of analog channels
- On/Off presentation of binary channels
- Display of current analog channels with scaling and limit markers
- Color change of bar graph to red when limits are infringed

### Numerical presentation




- Large numerical presentation of analog channels, including the channel name and description
- Each analog channel can be switched to the foreground
- On/Off presentation of binary channels

### Numerical 1-channel presentation




- Clear presentation of an analog channel
- An analog input is shown simultaneously as a bar graph and a number
- Display of channel name and description
- Display of scaling and limit markers

### Process image




- Freely configurable presentation (through the setup program) of analog and binary signals with background pictures
- One process image for each group

### Binary presentation




- On/Off presentation of binary channels

### Report



- Display of different reports for the analog channels of a group
- Details of minimum, maximum, average/integral values and time period
- Display of the previous report


### Batch reports



- 3 batches documented simultaneously
- Changeover between current and completed batch reports
- Electronic signature is possible
- Batch texts via interface and barcode reader, among others




## Counter/integrator presentation




- Presentation of up to 27 counters or integrators
- Changeover between individual and overall display
- Display of the current and the most recently completed count

## Group selection



- Up to 9 groups are configurable
- Up to 6 analog and 6 binary channels can be shown for each group
- Measurement signals can be used in several groups

## History presentation



- All stored measurement data are shown as curves at different zoom levels
- Display of scaling and limit markers of a channel
- Numerical display of the measurements of the analog channels at the cursor position
- Shifting of the visible section within the stored measurement data

## Presentation of alarm lists

| Date       | Time     | Description          |
|------------|----------|----------------------|
| 2006/07/04 | 09:47:22 | Alarm Lim02          |
| 2006/07/04 | 09:47:15 | Alarm Lim01          |
| 2006/07/04 | 09:47:15 | I/O 9 not calibrated |
| 2006/07/04 | 09:47:15 | High Alarm AIO8      |
| 2006/07/04 | 09:47:15 | I/O 8 not calibrated |
| 2006/07/04 | 09:47:15 | I/O 7 not calibrated |
| 2006/07/04 | 09:47:15 | High Alarm AIO2      |


- Display of current alarms
- For the instrument as a whole or batch-related
- Up to 150 entries visible on the recorder

## Presentation of event lists

| Date       | Time     | Description       |
|------------|----------|-------------------|
| 2006/07/04 | 09:35:19 | CF card removed   |
| 2006/07/04 | 09:35:19 | CF card in place  |
| 2006/07/04 | 09:35:16 | CF card removed   |
| 2006/07/04 | 09:34:16 | POWER ON          |
| 2006/07/04 | 09:33:42 | POWER OFF         |
| 2006/07/04 | 09:26:29 | Batch 01 end      |
| 2006/07/04 | 09:25:28 | Batch 01 start    |
| 2006/07/04 | 09:05:31 | NEW CONFIGURATION |



- Display and storage of events and alarms
- For the instrument as a whole or batch-related
- Up to 150 entries visible on the recorder

## Configuration



- Configuration on the recorder itself, by rotating and pressing the control knob
- Configuration through the setup program

## Visualization through the web browser




- Online visualization of a recorder
- Selection of (max.) three customized HTML pages (created on request)
- Navigation through the different recorder visualizations (curves, bar graph, text, process, ...)
- Max. four recorders or four different visualizations simultaneously

## PC programs

### PC Evaluation Software (PCA3000)

The PC Evaluation Software (PCA3000) is a program which runs under Windows 2000/XP, and is used to manage, archive, visualize and evaluate the recorder data.




- The data from differently configured instruments are recognized by the PC Evaluation Software and stored in an archive database. All management is fully automatic. The user only has to manually allocate an identifier (supplementary description).
- The user can at any time gain access to certain data sets which can be distinguished by the identifier. It is also possible to restrict the time periods to be evaluated.
- Any analog or binary channels of a paperless recorder (even from different groups) can subsequently be combined into PCA groups in PCA3000.
- Since each group is displayed in a separate window, several groups can be shown simultaneously on the screen and compared.
- Operation by mouse or keys.
- Using the export filter, it is possible to export the stored data, so that they can be processed in other programs such as Excel.
- The PC Evaluation Software PCA3000 has network capability, i.e. several users can obtain data from the same archive file (\*.177) in a network directory, independently of each other.

### PCA Communications software (PCC)

- Data can be read out from the recorder via the USB device interface, the serial interface (RS232/RS485) or via the Ethernet interface. The data can be read manually or automatically (e.g. daily at 23.00 hrs).
- Data can also be retrieved via remote control, through a modem.

### Functional overview



## Interfaces

- USB interfaces (standard)
- RS232/RS485 interface (standard)
- RS232 interface for barcode reader (standard)
- Ethernet interface (standard)
- PROFIBUS-DP interface (extra code)

### USB interfaces

With USB interfaces, a distinction is made between the host and the device interface. A USB memory stick can be attached to the host interface. The device interface, in conjunction with a standard commercial USB cable, is used to operate the setup program.

The paperless recorder without stainless steel front has host and device interfaces connected in parallel on both the front and back panels, of which only one of each type can ever be used. The paperless recorder with stainless steel front has only one host and one device interface at the rear panel.

### RS232/RS485 interface

Current process data, as well as specific device data, can be read out via the RS232 or RS485 interface.

Data saved to the internal memory can also be read out in conjunction with the PC Evaluation Software PCA3000 and the PCA Communications Software (PCC).

The RS232 interface permits a maximum lead length of 15 m, the RS485 interface 1.2 km.

Connection is by a 9-pin SUB-D connector on the back of the instrument. Modbus (master and slave) protocols are available, and the transmission mode used is RTU (Remote Terminal Unit).

### RS232 for barcode reader

A barcode reader can be attached to the interface. The barcode reader can be used to start or stop batch reporting, and to set batch texts (customer information, batch number...).

The barcode reader can also be operated via the RS232/RS485 interface, and the RS232 interface for the barcode reader can also be used as a Modbus master or slave.

|                                  | USB Host/Device   | RS232 RS485 | Ethernet | PROFIBUS-DP | External CF card |
|----------------------------------|-------------------|-------------|----------|-------------|------------------|
| Read current measurement data    | yes (device only) | yes         | yes      | yes         | no               |
| Write current measurement data   | no                | yes         | yes      | yes         | no               |
| Read out stored measurement data | yes               | yes         | yes      | no          | yes              |
| Read /write configuration        | yes               | yes         | yes      | no          | yes              |
| Write user list                  | yes               | yes         | yes      | no          | yes              |

### Ethernet interface

The Ethernet interface can be used in local networks for the communication between the recorder and the setup program and the PCA Communications Software. The IP address is set permanently through the configuration on the instrument or in the setup program, or can be automatically received from a DHCP server.

The integrated web server allows simultaneous access by several PCs to 3 HTML and 3 batch pages.

Transmission protocol: TCP/IP

Network type: 10BaseT, 100BaseT

### PROFIBUS-DP interface

The recorder can be integrated into a fieldbus system according to the PROFIBUS-DP standard via the PROFIBUS-DP interface. This PROFIBUS version is especially designed for communication between automation systems and distributed peripheral devices at the field level.

Data are transmitted serially according to the RS485 standard, with a maximum 12 Mbits/sec.

Using the project design tool that is included in the delivery (GSD generator; GSD = device master file), an application-specific GSD file is created, which is used to integrate the recorder into the fieldbus system.

### External CompactFlash memory card (CF)

For paperless recorders without stainless steel front, the external CompactFlash memory card (CF) is used to transfer the data from the internal memory to the PC. Configuration data can be created on the PC and then transferred to the recorder by means of the memory card.

On the PC side, data on the card is accessed using a read/write device (CompactFlash reader/writer).

### External inputs via interface

The paperless recorder can acquire and store up to 24 external analog inputs and 24 binary inputs.

Furthermore, the interfaces can be used to enter comments in the event list of the recorder.

## Stainless steel front (extra code 444)

The paperless recorder with extra code 444 (without extra code 350) may be installed in switch cabinets with at least a simplified pressurized enclosure. Under these conditions, use in a potentially explosive atmosphere (max. zones 1 and 21) is authorized from the front.

Notes on installation in Installation Instructions B 70.6581.4.1 must be complied with and followed.

Paperless recorders with authorization for explosion hazard areas, carry the following mark on the nameplate attached to the instrument.

 II 2G Ex px IIC


 II 2D Ex pD 21 IP65

Caution: If extra code 444 is present, the CompactFlash memory card can no longer be used for external storage. Measurement data can be read out via one of the interfaces or via a USB memory stick (from the back).

## Connection diagram

Rear view with pluggable screw terminals

Instrument variant 1




**Module slot 3 (top)**  
fitted with one relay card.

**Module slot 2 (middle)**  
fitted with 6 analog channels or  
3 analog channels and  
8 binary inputs/outputs.

**Module slot 1 (bottom)**  
fitted with 6 analog channels or  
3 analog channels and  
8 binary inputs/outputs.















Instrument variant 2


















**Module slot 3 (top)**  
fitted with 6 analog channels or  
3 analog channels and  
8 binary inputs/outputs.

**Module slot 2 (middle)**  
fitted with 6 analog channels or  
3 analog channels and  
8 binary inputs/outputs.


**Module slot 1 (bottom)**  
fitted with 6 analog channels or  
3 analog channels and  
8 binary inputs/outputs.

| Terminal assignment             | Connector                                                                                                                                                                                                                                                                                                                                 | Diagram                                                                                                                           |
|---------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| <b>Supply</b>                   |                                                                                                                                                                                                                                                                                                                                           |                                                                                                                                   |
| Supply<br>as on nameplate       | Connector 4<br>L1 (L+)<br>N (L-)<br>PE<br>                                                                                                                                                                                                               |                                                |
| <b>Analog inputs</b>            |                                                                                                                                                                                                                                                                                                                                           |                                                                                                                                   |
| Thermocouple                    | Connectors 8 to 11<br>(input 1 to 12)<br>for instrument variant 1<br><br><br><br>or<br><br>Connectors 8 to 13<br>(input 1 to 18)<br>for instrument variant 2<br><br> |                                                |
| RTD in 2-wire circuit           |                                                                                                                                                                                                                                                                                                                                           |                                                |
| RTD in 3-wire circuit           |                                                                                                                                                                                                                                                                                                                                           |                                                |
| RTD in 4-wire circuit           |                                                                                                                                                                                                                                                                                                                                           |                                               |
| Resistance transmitter          |                                                                                                                                                                                                                                                                                                                                           |  <p>E = End<br/>S = Slider<br/>A = Start</p> |
| Potentiometer in 2-wire circuit |                                                                                                                                                                                                                                                                                                                                           |                                              |
| Potentiometer in 3-wire circuit |                                                                                                                                                                                                                                                                                                                                           |                                              |
| Potentiometer in 4-wire circuit |                                                                                                                                                                                                                                                                                                                                           |                                              |
| Voltage input 0 - 1V            |                                                                                                                                                                                                                                                                                                                                           |  <p><math>U_x = 0 \dots 1V</math></p>        |
| Voltage input 0 - 10V           |                                                                                                                                                                                                                                                                                                                                           |  <p><math>U_x = 0 \dots 10V</math></p>       |
| Current input                   |                                                                                                                                                                                                                                                                                                                                           |  <p><math>I_x</math></p>                     |


| Terminal assignment                                                                                                                                                                                                                     | Connector                                                                                                                                                                                                                                                                                                  | Diagram                                                                                                                                                                                                                                                                                                                                                    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Binary inputs/outputs</b><br> Configuration (through the setup program or on the instrument) defines which are binary inputs and which are outputs. |                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                                                                                            |
| <b>B1 ... B8</b><br><br>voltage-controlled<br>LOW = -3 to +5V DC<br>LOW = 12 to 30V DC<br><br>internal power supply 24V/60mA ( $U_{out}$ )<br><br>     | Connector 9<br>only on modules with<br>3 analog inputs<br><br>B1    binary input/<br>output 1<br><br>...<br>B8    binary input/<br>output 8<br><br>$U_{in+}$ external power<br>supply<br>$U_{in-}$ ground<br>$U_{out+}$ +24V internal<br>power supply<br>$U_{out-}$ ground                                 | <br><br>Example:<br>Connecting a load to binary output 4 (B4) and a solid-state relay to binary output 3 (B3) requires an external power supply.<br><br>Diagram of the connector:<br> |
| <b>B9 ... B16</b><br><br>voltage-controlled<br>LOW = -3 to +5V DC<br>LOW = 12 to 30V DC<br><br>internal power supply 24V/60mA ( $U_{out}$ )<br><br>  | Connector 11<br>only on modules with<br>3 analog inputs<br><br>B9    binary input/<br>output 9<br><br>...<br>B16   binary input/<br>output 16<br><br>$U_{in+}$ external power<br>supply<br>$U_{in-}$ ground<br>$U_{out+}$ +24V internal<br>power supply<br>$U_{out-}$ ground                               | <br><br>Example:<br>Binary input 12 (B12) is operated from the internal power supply.<br><br>Diagram of the connector:<br>                                                        |
| <b>B17 ... B24</b><br><br>voltage-controlled<br>LOW = -3 to +5V DC<br>LOW = 12 to 30V DC<br><br>internal power supply 24V/60mA ( $U_{out}$ )<br><br> | Connector 13<br>only for instr. variant 2<br>and for modules with<br>3 analog inputs<br><br>B17   binary input/<br>output 17<br><br>...<br>B24   binary input/<br>output 24<br><br>$U_{in+}$ external power<br>supply<br>$U_{in-}$ ground<br>$U_{out+}$ +24V internal<br>power supply<br>$U_{out-}$ ground | <br><br>Example:<br>Binary input 20 (B20) is operated from the internal power supply.<br><br>Diagram of the connector:<br>                                                        |

| Terminal assignment                                                | Connector                                                                                                                                 | Diagram                                                                                                                                                                                               |
|--------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Relay outputs                                                      |                                                                                                                                           |                                                                                                                                                                                                       |
| Relay 1<br>changeover (SPDT)                                       | Connector 1<br>                                          |                                                                                                                    |
| Relay 2<br>changeover (SPDT)                                       | <br>Connector 14<br><br>only for instrument<br>variant 1 |                                                                                                                    |
| Relay 3<br>changeover (SPDT)                                       |                                                                                                                                           |                                                                                                                    |
| Relay 4<br>changeover (SPDT)                                       |                                                                                                                                           |                                                                                                                    |
| Relay 5<br>changeover (SPDT)                                       |                                                                                                                                           |                                                                                                                    |
| Relay 6<br>changeover (SPDT)                                       |                                                                                                                                           |                                                                                                                   |
| Relay 7<br>changeover (SPDT)                                       |                                                                                                                                           |                                                                                                                  |
| Interfaces                                                         |                                                                                                                                           |                                                                                                                                                                                                       |
| RS232 for barcode reader<br>9-pin SUB-D socket connector           | Connector 2<br>                                        | 2 RxD      Receive Data<br>3 TxD      Transmit Data<br>5 GND      Ground                                                                                                                              |
| PROFIBUS-DP<br>9-pin SUB-D socket connector<br>(extra code)        | Connector 3<br>                                        | 3 RxD/TxD-P      Receive/Transmit Data-Pos.<br>B conductor<br>5 DGND      Ground for data transmission<br>6 VP      Supply voltage-Pos.<br>8 RxD/TxD-P      Receive/Transmit Data-Neg.<br>A conductor |
| USB host interface<br>for connecting memory sticks                 | Connector 5<br>                                        | The recorder without stainless steel front also has a USB host interface on the front panel, connected in parallel. The two interfaces cannot both be operated at the same time.                      |
| Ethernet<br>RJ45 socket connector                                  | Connector 6<br>                                        | 1 TX+      Transmit Data +<br>2 TX-      Transmit Data -<br>3 RX+      Receive Data +<br>6 RX-      Receive Data -                                                                                    |
| RS232<br>9-pin SUB-D socket connector<br><br>(switchable to RS485) | Connector 7<br>                                        | 2 RxD      Receive Data<br>3 TxD      Transmit Data<br>5 GND      Ground                                                                                                                              |
| RS485<br>9-pin SUB-D socket connector<br><br>(switchable to RS232) | Connector 7<br>                                        | 3 TxD+/RxD+      Transmit/Receive Data +<br>Ground<br>5 GND      Ground<br>8 TxD-/RxD-      Transmit/Receive Data -                                                                                   |




| Terminal assignment                       | Connector                                                                                         | Diagram                                                                                                                                                                            |
|-------------------------------------------|---------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| USB host interface<br>for connecting a PC | Connector 15<br> | The recorder without stainless steel front also has a USB device interface on the front panel, connected in parallel. The two interfaces cannot both be operated at the same time. |

## Overview of the electrical isolation




## Dimensions


Recorder with die-cast zinc front




Recorder with stainless steel front (extra code 444)



Panel cut-out



## Universal carrying case option - TG-35



## Order details

|                |     |                                                                                                                                  |                   |
|----------------|-----|----------------------------------------------------------------------------------------------------------------------------------|-------------------|
|                |     | <b>Basic type</b>                                                                                                                |                   |
| <b>706581/</b> |     | Paperless recorder with Ethernet, USB and RS232/RS485 interfaces and RS232 interface (to connect a barcode reader) and one relay |                   |
|                |     | <b>Basic type extensions</b>                                                                                                     |                   |
|                |     | <b>Software</b>                                                                                                                  |                   |
| 0              |     | No software package                                                                                                              |                   |
| 1              |     | With software package (setup program incl. USB cable, PC Evaluation software PCA3000, PCA Communications software PCC)           |                   |
|                |     | <b>Language for instrument texts</b>                                                                                             |                   |
| 8              |     | Factory setting (English/German)                                                                                                 |                   |
| 9              |     | Set to customer specification                                                                                                    |                   |
|                |     | <b>Module slots</b>                                                                                                              |                   |
|                |     | <b>Slot 1 (bottom)</b>                                                                                                           |                   |
| 0              |     | not used                                                                                                                         |                   |
| 2              |     | 3 analog inputs and 8 binary inputs/outputs                                                                                      |                   |
| 3              |     | 6 analog inputs                                                                                                                  |                   |
|                |     | <b>Slot 2 (middle)</b>                                                                                                           |                   |
| 0              |     | not used                                                                                                                         |                   |
| 2              |     | 3 analog inputs and 8 binary inputs/outputs                                                                                      |                   |
| 3              |     | 6 analog inputs                                                                                                                  |                   |
|                |     | <b>Slot 3 (top)</b>                                                                                                              |                   |
| 0              |     | not used                                                                                                                         |                   |
| 1              |     | 6 relay outputs                                                                                                                  |                   |
| 2              |     | 3 analog inputs and 8 binary inputs/outputs                                                                                      |                   |
| 3              |     | 6 analog inputs                                                                                                                  |                   |
|                |     | <b>Supply</b>                                                                                                                    |                   |
| 33             |     | 100 - 240V AC +10/-15%, 48 - 63Hz                                                                                                |                   |
| 25             |     | 20 - 30V AC/DC, 48 - 63Hz                                                                                                        |                   |
|                |     | <b>Extra codes</b>                                                                                                               |                   |
| 020            |     | Lithium battery for memory buffering (ex-factory)                                                                                |                   |
| 021            |     | Storage capacitor (instead of extra code 020)                                                                                    |                   |
| 260            |     | Math and logic module                                                                                                            |                   |
| 267            |     | PROFIBUS-DP interface                                                                                                            |                   |
| 350            |     | Universal carrying case TG-35 <sup>1</sup>                                                                                       |                   |
| 444            |     | Stainless steel front with touchpad         |                   |
| 706581/        |     | -                                                                                                                                |                   |
| 706581/        | 1 8 | -                                                                                                                                | 3 2 1             |
|                |     | -                                                                                                                                | 33                |
|                |     | /                                                                                                                                | 020               |
|                |     |                                                                                                                                  | ,... <sup>2</sup> |
|                |     |                                                                                                                                  | (Order code)      |
|                |     |                                                                                                                                  | (Order example)   |

<sup>1</sup> This extra code is available in combination with supply voltage 100—240V AC, not with low supply voltage.  
UL and ATEX approvals not applicable. The protection type in the carrying case corresponds to IP20, outside IP20D.

<sup>2</sup> List extra codes in sequence, separated by commas.

## Standard accessories

- 1 Installation instructions B 70.6581.4 (B 70.6581.4.1 with extra code 444) and 1 Operating instructions B 70.6581.1
- 4 mounting brackets
- 1 control panel seal
- 1 CD with detailed operating instructions and additional documentation

## Accessories - data sheet 70.9700

- CompactFlash memory cards and USB memory sticks. The CF cards and memory sticks specified by JUMO are tested and designed for industrial applications. Other makes cannot be guaranteed.
- For further accessories, see data sheet 70.9700.