

# CHEMTRONICS®

## Technical Data Sheet

TDS #CFP50

### Foamtips™ Pro

#### PRODUCT DESCRIPTION

**Chemtronics® Foamtips™ Pro Swabs** are constructed from medical grade foam which features the best open cell structure, providing excellent particle entrapment characteristics. The foam is thermally bonded to the swab handle without using adhesives. These swabs are the most economical and are ideal for general applications.

- Traps surface particles while cleaning
- High solvent capacity; holds solvent well
- Fiberless construction does not generate loose fibers or particles
- No adhesives or binders are used in the construction
- Economical for high quantity applications

#### TYPICAL APPLICATIONS

**Chemtronics® Foamtips™ Pro Swabs** can be used to:

- Clean Excess Adhesives After Gluing
- Remove Contamination from Disk Drives
- Micro Mechanical Cleaning
- Maintenance and Care of Fax machines VCR's PC's Printers, and Copiers
- Remove flux residue from printed circuit boards
- Good for general purpose cleaning

#### SWAB DIMENSIONS

Dual heads:

- 100 PPI open cell foam 7/8" long, 1/2" wide, 3/8" thick
- 75 PPI closed cell foam 13/16" long, 9/32" wide, 3/8" thick

#### COMPATIBILITY

Foam Heads are compatible with most common solvents such as isopropyl alcohol, and methanol.

Not recommended for use with ketones such as acetone or methyl ethyl ketone.

Polypropylene Handles are generally compatible with all common solvents including most dilute or weak acids.

#### AVAILABILITY

**CFP50** 6-3/4 " (17 cm) Handle, dual foam heads  
50 swabs / bag

#### TECHNICAL AND APPLICATION ASSISTANCE

ITW Chemtronics provides a technical hotline to answer your technical and application related questions. The toll free number is: **1-800-TECH-401**.

#### MANUFACTURED BY:

ITW CHEMTRONICS®  
8125 Cobb Center Drive  
Kennesaw, GA 30152 USA  
1-770-424-4888

REV. (05/04)

Chemtronics® is a registered trademark of ITW Chemtronics. All rights reserved.

Foamtips™ is a trademark of ITW Chemtronics. All rights reserved.

#### DISTRIBUTED BY: