

Shut Off Valve

Series **VHS**

3-Port Valve for Residual Pressure Release (V)

Features

- Relieves the downstream pressure for system servicing.
- Can be locked in off state with padlock.
- Visual position indication.
- Red handle for easy location on machine.

Specifications

Model	Port size		Effective area (mm ²) () Effective Area mm ² (Cv)	
	IN, OUT	EXH.	IN to OUT	OUT to EXH.
VHS20	1/8	1/8	10 (0.54)	11 (0.60)
	1/4		14 (0.76)	16 (0.87)
VHS30	1/4	1/4	16 (0.87)	14 (0.76)
	3/8		31 (1.68)	29 (1.57)
VHS40	1/4	3/8	27 (1.46)	36 (1.95)
	3/8		38 (2.06)	40 (2.17)
	1/2		55 (2.98)	42 (2.28)
VHS40-06	3/4	1/2	77 (1.73)	49 (2.66)
VHS50	3/4	1/2	82 (4.44)	50 (2.71)
	1		125 (6.78)	53 (2.87)

Note) Use an air filter on the IN side for operating protection.

How to order

VHS 30 - F 03 - R

3-port valve for residual pressure release

Body size

Symbol	Applicable model
20	AC20
30	AC25, 30
40	AC40
50	AC50, AC60>Note)

Note) When the valve is mounted on 60 size, the flow rate may decrease depending upon the mounting position.

Thread type

F	G
---	---

Port size



Symbol	Port size	Body size			
		20	30	40	50
01	1/8	●	—	—	—
02	1/4	●	●	●	—
03	3/8	—	●	●	—
04	1/2	—	—	●	—
06	3/4	—	—	●	●
10	1	—	—	—	●

Optional specifications



Code	Description
Nil	Flow direction: Left to right
R	Flow direction: Right to left



With the use of a 3-port valve for residual pressure release, pressure left in the line can be easily exhausted.



Symbol



Model	A	B	C	D	E	F	G	H	I
VHS20	59	20	40	34	—	45	33	28	45
VHS30	78	29	53	46	—	55	42	30	55
VHS40	107	39	70	63	22	58	44	36	63
VHS40-06	110	42	75	67	21	65	50	44	69
VHS50	134	53	90	78	26	76	61	54	81

Caution

- Consult SMC when a pressure switch and T type spacer are installed on the outlet of pressure release valve
- If a stop valve or a silencer is connected to the exhaust port of VHS20/30, the effective sectional area should be larger than the figure indicated in the following table, to prevent malfunction caused by back pressure. (This is not applicable to VHS40 and VHS50)

Model	Effective area (mm ²)
VHS20	5
VHS30	5