Schmitt Input, Non-Inverting TTL Output Receiver

FEATURES

- Converts fiber optic input signals to TTL totem pole outputs
- Maximum sensitivity 1.5 μW peak (-28.2 dBm)
- Wide variety of cable options, operates with 50/125, 62.5/125, and 100/140 µm cables
- Schmitt circuitry gives 17dB minimum dynamic range and low Pulse Width Distortion
- · Operates up to 200K bps NRZ
- · Designed to operate with Honeywell 850 nm LEDs
- · Single 5 V supply requirement
- Wave solderable
- · Mounting options

SMA single hole ST single hole SMA PCB ST PCB SMA 4 hole

DESCRIPTION

The HFD3029-002/XXX is a sensitive Schmitt triggered optical receiver designed for use in short distance, 850 nm fiber optic systems. The bipolar integrated receiver circuit has internal voltage regulation. The HFD3029-002/XXX also uses an internal photodiode. The TTL non-inverting output allows the HFD3029-002/XXX to be directly interfaced with standard digital TTL circuits.

APPLICATION

The HFD3029-002/XXX fiber optic receiver converts the optical signal in a point to point data communications fiber optic link to a TTL output. It is mounted in a fiber optic connector that aligns the optical axis of the component to the axis of the optical fiber.

Electrical isolation is important in obtaining the maximum performance of this high sensitivity receiver. Shielding can reduce coupled noise and allow maximum sensitivity to be obtained. This can include the use of ground planes in the PCB, shielding around the device, and shielding around the leads.

Schmitt Input, Non-Inverting TTL Output Receiver

APPLICATION (continued)

An internal voltage regulator allows operation with a 5 volt supply. An external bypass capacitor (0.1 μ F) between V_{CC} (pin 1) and ground (pin 3) is recommended for maximum power supply noise rejection.

Honeywell also offers companion transmitters designed to operate in conjunction with the HFD3029-002/XXX.

Optical power (photons) from the fiber strikes the photodiode and is converted to electrical current. The current is converted into voltage in the transimpedance preamplifier. The Schmitt trigger circuitry in the comparator stage provides proper output signals. The Schmitt detection circuit monitors the input preamplifier, and triggers when its output exceeds present levels. Preset levels are above worst case RMS noise level, with 1 x 10-9 bit error rate, while low enough for enough sensitivity to allow operation over long links. This circuitry recognizes positive and negative going input signals. When the optical input goes from low to high, the electrical output changes to "1" (high). The output changes to "0" (low) when the optical input goes from high to low. Bandwidth has been limited to minimize noise problems. The output of the Schmitt Trigger detector stage is designed for good pulse width distortion (PWD).



Schmitt Input, Non-Inverting TTL Output Receiver

ELECTRO-OPTICAL CHARACTERISTICS (V_{CC} = 5.0 V ±0.5 VDC, -40°C < T_C < +85°C unless otherwise stated)

| PARAMETER | SYMBOL | MIN | TYP | MAX | UNITS | TEST CONDITIONS |
|-----------------------------------|------------------------|-----|-----|-----|-------|--|
| Minimum Input Sensitivity T= 25°C | P _{IN} (Peak) | | 1 | 1.5 | μW | 100 µm core fiber Duty Cycle = 50%, 850 µm |
| High Level Logic Output Voltage | Vон | 2.4 | 3.3 | | V | $P_{IN} \ge 1.5 \mu W$, $V_{CC} = 5.0 VDC$ |
| Low Level Logic Output Voltage | VoL | | 0.3 | 0.4 | V | $P_{IN} \le 0.1 \ \mu W, \ V_{CC} = 5.0 \ VDC$ |
| | | | | | | I _O ≤ 16 mA |
| Power Supply Current | lcc | | 6 | 12 | mA | |
| Rise Time | t _R | | 12 | | ns | $P_{IN} \ge 1.5 \mu W$, $V_0 = 0.4 \text{ to } 2.4 \text{ V}$ |
| Fall Time | t⊧ | | 3 | | ns | $P_{IN} \le 0.1 \mu W$, $V_0 = 2.4 \text{ to } 0.4 \text{V}$ |
| Pulse Width Distortion | PWD | | | | % | f = 20 kHz, Duty Cycle = 50% |
| T = 25°C | | | 5 | 10 | | P _{IN} ≥ 1.5 µW peak |
| | | | 5 | 10 | | P _{IN} ≥ 100 μW |
| Bandwidth | BW | | | 200 | kHz | P _{IN} ≥1.0µW, Duty Cycle = 50% |
| Output Impedance | lo | | 20 | | Ω | |

ABSOLUTE MAXIMUM RATINGS

(Tcase = 25°C unless otherwise noted)

Storage temperature -40 to +100°C
Supply voltage +4.5 to +7.0 V
Lead solder temperature 260°C for 10 s

Junction temperature 150°C

Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.

RECOMMENDED OPERATING CONDITIONS

Operating temperature $-40 \text{ to } +100^{\circ}\text{C}$ Supply voltage +4.5 to +7.0 VOptical input power $1.5 \text{ to } 100 \text{ } \mu\text{W}$ Optical signal pulse width $> 4 \text{ } \mu\text{s}$





Schmitt Input, Non-Inverting TTL Output Receiver

ORDER GUIDE

| Description | Catalog Listing |
|--------------------------------|-----------------|
| Fiber Optic Schmitt Input, Non | HFD3029-002/XXX |
| inverting, TTL Output Receiver | |

MOUNTING OPTIONS

Substitute XXX with one of the following 3 letter combinations

 SMA single hole
 - AAA

 ST single hole
 - BAA

 SMA PCB
 - ABA

 ST PCB
 - BBA

 SMA 4 hole
 - ADA

 Dimensions on page 441

CAUTION


The inherent design of this component causes it to be sensitive to electrostatic discharge (ESD). To prevent ESD-induced damage and/or degradation to equipment, take normal ESD precautions when handling this product.




FIBER INTERFACE

Honeywell detectors are designed to interface with multimode fibers with sizes (core/cladding diameters) ranging from 50/125 to 200/230 microns. Honeywell performs final tests using 100/140 micron core fiber. The fiber chosen by the end user will depend upon a number of application issues (distance, link budget, cable attenuation, splice attenuation, and safety margin). The 50/125 and 62.5/125 micron fibers have the advantages of high bandwidth and low cost, making them ideal for higher bandwidth installations. The use of 100/140 and 200/230 micron core fibers results in greater power being coupled by the transmitter, making it easier to splice or connect in bulkhead areas. Optical cables can be purchased from a number of sources.

BLOCK DIAGRAM



SWITCHING WAVEFORM





Schmitt Input, Non-Inverting TTL Output Receiver

Fig. 1 Pulse Width Distortion vs Temperature




Fig. 3 Pulse Width Distortion vs Optical Input Power




Fig. 2 Pulse Width Distortion vs Frequency





Fig. 4 Propagation Delay vs Optical Input Power




European Connectorized Receivers

Honeywell receiver components are available in the following connector styles. Each style has a three-digit reference used in the order guides.


SMA SINGLE HOLE MOUNTING (REF.: AAA)







ST SINGLE HOLE MOUNTING (REF.: BAA)





SMA PCB MOUNTING (REF.: ABA)






Honeywell Optoelectronics reserves the right to make changes at any time in order to improve design and supply the best products possible.

European Connectorized Receivers

ST PCB MOUNTING (REF.: BBA)



SMA 4 HOLE MOUNTING (REF.: ADA)



