

TRADITIONAL MINIATURE JOYSTICK SPECIFICATIONS:

- Joystick travel - 25° from design center in all directions
- Mechanical lifecycle - 5,000,000 (minimum)
- Main pivot ball - precision ground stainless steel
- Stick shaft - 3/16in. brass plated
- Return to center repeatability - $\pm 2\%$
- Mounting - front or rear panel (see bezels)
- Panel thickness (mounting) - .050in. to .1875in.
- Deflection force - .18 lbs @ 25° 1 1/2in. up from pivot point
- Potentiometer calibration - thumb tab provides up to 180° of calibration
- Potentiometers - set at center of resistance

CH PRODUCTS

OEM INDUSTRIAL DIVISION

Home

Products

Configuration Guides

Sales Reps

Technical Specifications

About Us

Contact Us

-  OEM Home
-  **Configuration Guides**
 - Traditional
 - HFX Standard
 - HFX Hand Grip
 - HFX Fader
 - Trackball

CH Products
970 Park Center Dr.
Vista, CA 92081
Tele 760-598-2518
Tele (USA Only)
FAX 760-598-2524



Configuration Guides

[Traditional Configuration Guide](#) | [HFX Standard Joysticks Configuration Guide](#)
[HFX Hand Grip Joysticks Configuration Guide](#) | [HFX T-Bar Fader Configuration Guide](#)
[Trackball Configuration Guide](#)

Traditional Joysticks Part Number Configuration & Availability Guide

Description Key Feature Feature Availability

Joystick Type	S	Standard	S	S	S	S								
	M	Miniature					M	M	M	M				
	C	Compact									C	C	C	C

Model Number	1	100-2 Axis	100					100				100			
	2	200-2 Axis with Pushbutton		200				200				200			
	3	300-3 Axis				300				300				300	
	4	400-3 Axis with Pushbutton					400					400			400
Construction	0	Nylon plastic	X	X	X	X						X	X	X	X
	1	Glass-filled nylon						X	X	X	X				

Mounting Bezel	A	Round Cup -Textured (FM)	X												
	C	Split Bezel -Textured (FM)	X	X	X	X	X	X	X	X					
	F	Square Bezel -Textured (RM)	X					X							

	O	Computer Bezel	X	X	X	X					X	X	X	X
	L	Rubber Boot Kit (FM)	X	X	X	X	X	X	X	X				
	Q	Square Bezel Snap-On (FM)	X				X							
	U	Round Bezel Snap-On (FM)	X	X	X	X								
	X	Without Bezel	X	X	X	X	X	X	X	X				

Centering	0	Spring Centering	X	X	X	X	X	X	X	X	X	X	X	X	X
	1	Friction Clutch	X	X	X	X									
	3	Center Detent - X Axis	X	X	X	X									
	4	Center Detent - Y Axis	X	X	X	X									
	5	Center Detent Both Axis	X	X	X	X									
	6	Torque Set (friction)	X	X	X	X	X	X	X	X	X				

Stick Handle	0	Tapered Convex	X				X				X				
	1	Concave Tip	X				X				X				
	2	Flat Tipped	X				X				X				
	3	Concave Tip - Long	X				X				X				
	5	Pushbutton		X				X				X			
	6	Straight Tip - Short	X				X				X				
	8	3rd Axis - Model B			X				X				X		
	9	3rd Axis with Pushbutton				X				X				X	
	A	Straight Tip - Mid	X				X				X				
	B	Straight Tip - Long	X				X				X				
	C	Ball Tip	X				X				X				
	E	Pushbutton - Option E		X				X				X			
	G	Pushbutton - Option G		X				X				X			

	H	Pushbutton - Option H		X					X				X		
	K				X						X			X	
	X	Without Handle	X					X				X			
Trim	0	Above Panel Trim	X	X	X	X					X	X	X	X	
	1	Below Panel Trim	X	X	X	X	X	X	X	X	X	X	X	X	
	9	Unassembled	X	X	X	X	X	X	X	X					
Output Options		Potentiometer													
	F	Clarostat 595 5K	X	X	X	X	X	X	X	X	X	X	X	X	X
	C	Clarostat 388 10K	X	X	X	X	X	X	X	X	X	X	X	X	X
	J	CTS (HP100) 100K	X	X	X	X						X	X	X	X
	L	CTS (HP130) 130K	X	X	X	X						X	X	X	X
	R	Nei Sensorcube 5K	X	X	X	X	X	X	X	X	X	X	X	X	X
	U	Nei Sensorcube 10K	X	X	X	X						X	X	X	X
	W	Without Pot	X	X	X	X	X	X	X	X					
	Z	Special Pot	X	X	X	X									
		Hall Effect Side Plate													
	0	0V to 5V rail-to-rail	X	X	X	X	X	X	X	X					
	1	0.5V to+ 4.5V w/Fault Detection	X	X	X	X	X	X	X	X					
	2	.025V to 4.75V w/Fault Detection	X	X	X	X	X	X	X	X					
	3	2V to 3V	X	X	X	X	X	X	X	X					
	4	1V to 4V	X	X	X	X	X	X	X	X					

*The O bezel is only available on Standard Joysticks that are placed in the SJ Housing.

Product names used herein are for identification purposes only and may be trademarks of their respective companies.