


Clairex[®]
Technologies, Inc.

March, 2002



features

- 0.020" dia. light pipe aperture
- T0-72 package
- NPN buffer open collector output

description

The CLI700 consists of an 880nm AlGaAs IRED and an NPN, buffer, open collector photo-IC mounted on a custom TO-72 header. The IRED emits a broad radiation pattern through the formed clear epoxy lens. Radiation reflected from the target is received by a 0.020" diameter fiber optic light pipe attached to the active area of the photo-IC.

absolute maximum ratings ($T_A = 25^\circ\text{C}$ unless otherwise stated)

storage temperature	-40°C to +125°C
operating temperature	-40°C to +100°C
lead soldering temperature	260°C
IRED	
continuous forward DC current	35mA
reverse DC voltage	5V
power dissipation ⁽¹⁾	100mW
PHOTO-IC	
supply voltage	15V
output sink current	25mA

note:

1. Derate linearly 1.33mW/°C from 25°C free air temperature to $T_A = +100^\circ\text{C}$.

definition: Output is buffer, open collector. Output is HIGH (OFF) when reflected light is sensed and LOW (ON) when reflected light is not sensed.

electrical characteristics (T _A = 25°C and V _{CC} = 5.0V unless otherwise noted)						
symbol	parameter	min	typ	max	units	test conditions
V _F	IRED forward voltage	1.40	1.50	1.65	V	I _F = 20mA
I _R	IRED reverse current	-	-	10	μA	V _R = 5V
λ _P	Peak emission wavelength	-	880	-	nm	I _F = 20mA
BW	Spectral bandwidth at half power points	-	80	-	nm	I _F = 20mA
I _{CC}	Sensor supply current	-	4.0	10.0	mA	V _{CC} =15V
V _{OL}	Low level output voltage	-	0.3	0.5	V	I _C = 15mA
		-	0.5	0.8	V	I _C = 25mA
I _{OH}	High level output current	-	-	1.0	μA	I _F = 35mA ⁽¹⁾
I _{FT}	Turn-on threshold (IRED current)	-	-	7.0	mA	d = 0.03 inches ⁽²⁾
I _F (+)/I _F (-)	Hysteresis	-	12	-	%	
t _r , t _f	Output rise and fall time	-	200	500	ns	R _L =200Ω, duty cycle = 50%
t _p	Propagation delay	-	-	80	μs	R _L =200Ω, duty cycle = 50%

- notes:** 1. No reflective surface.
2. Measured using a Kodak 90% diffuse reflectance neutral white test card.

Clairex reserves the right to make changes at any time to improve design and to provide the best possible product.

Revised 10/29/02

Clairex Technologies, Inc.
Phone: 972-422-4676

1845 Summit Ave., #404
Fax: 972-423-8628

Plano, Texas 75074-8148
www.clairex.com